

| 化合物名 | 構造式 | 名称 | CAS | 分子量 (Mn) | 製品コード |
|--------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------|-----|----------|-------------|
| 三臂聚乙二醇 3-arm Poly(ethylene glycol) | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\right\}_3$ | 3-arm PEG-OH | | 2,000 | 06020600102 |
| | | | | 5,000 | 06020600106 |
| | | | | 10,000 | 06020600109 |
| | | | | 20,000 | 06020600112 |
| 三臂聚乙二醇羧酸 3-arm Poly(ethylene glycol) carboxylic acid | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\text{-CH}_2\text{-COOH}\right\}_3$ | 3-arm PEG-CM | | 2,000 | 06020600402 |
| | | | | 5,000 | 06020600406 |
| | | | | 10,000 | 06020600409 |
| | | | | 20,000 | 06020600412 |
| 三臂聚乙二醇琥珀酸 (酯键) 3-arm Poly(ethylene glycol) succinate acid | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\text{-C}\left(\text{O}\right)\text{-CH}_2\text{CH}_2\text{-C}\left(\text{O}\right)\text{-OH}\right\}_3$ | 3-arm PEG-SA | | 2,000 | 06020600702 |
| | | | | 5,000 | 06020600706 |
| | | | | 10,000 | 06020600709 |
| | | | | 20,000 | 06020600712 |
| 三臂聚乙二醇琥珀酸 (酰胺键) 3-arm Poly(ethylene glycol) succinimidyl acid | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\text{-CH}_2\text{CH}_2\text{-NH-C}\left(\text{O}\right)\text{-CH}_2\text{CH}_2\text{-C}\left(\text{O}\right)\text{-OH}\right\}_3$ | 3-arm PEG-SAA | | 2,000 | 06020600802 |
| | | | | 5,000 | 06020600806 |
| | | | | 10,000 | 06020600809 |
| | | | | 20,000 | 06020600812 |
| 三臂聚乙二醇戊酸 (酯键) 3-arm Poly(ethylene glycol) glutarate acid | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\text{-CH}_2\text{CH}_2\text{CH}_2\text{-C}\left(\text{O}\right)\text{-OH}\right\}_3$ | 3-arm PEG-GA | | 2,000 | 06020601102 |
| | | | | 5,000 | 06020601106 |
| | | | | 10,000 | 06020601109 |
| | | | | 20,000 | 06020601112 |
| 三臂聚乙二醇戊酸 (酰胺键) 3-arm Poly(ethylene glycol) glutamidyl acid | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\text{-CH}_2\text{CH}_2\text{NH-C}\left(\text{O}\right)\text{-CH}_2\text{CH}_2\text{CH}_2\text{-C}\left(\text{O}\right)\text{-OH}\right\}_3$ | 3-arm PEG-GAA | | 2,000 | 06020601002 |
| | | | | 5,000 | 06020601006 |
| | | | | 10,000 | 06020601009 |
| | | | | 20,000 | 06020601012 |
| 三臂聚乙二醇胺 3-arm Poly(ethylene glycol) amine | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\text{-CH}_2\text{CH}_2\text{-NH}_2\right\}_3$ | 3-arm PEG-NH ₂ | | 2,000 | 06020600202 |
| | | | | 5,000 | 06020600206 |
| | | | | 10,000 | 06020600209 |
| | | | | 20,000 | 06020600212 |
| 三臂聚乙二醇胺盐酸盐 3-arm Poly(ethylene glycol) amine hydrochloride salt | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\text{-CH}_2\text{CH}_2\text{-NH}_2\text{HCl}\right\}_3$ | 3-arm PEG-NH ₂ HCl | | 2,000 | 06020608102 |
| | | | | 5,000 | 06020608106 |
| | | | | 10,000 | 06020608109 |
| | | | | 20,000 | 06020608112 |
| 三臂聚乙二醇硫醇 3-arm Poly(ethylene glycol) thiol | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\text{-CH}_2\text{CH}_2\text{-SH}\right\}_3$ | 3-arm PEG-SH | | 2,000 | 06020601302 |
| | | | | 5,000 | 06020601306 |
| | | | | 10,000 | 06020601309 |
| | | | | 20,000 | 06020601312 |
| 三臂聚乙二醇丙醛 3-arm Poly(ethylene glycol) propionaldehyde | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\text{-CH}_2\text{CH}_2\text{-CHO}\right\}_3$ | 3-arm PEG-pALD | | 2,000 | 06020601402 |
| | | | | 5,000 | 06020601406 |
| | | | | 10,000 | 06020601409 |
| | | | | 20,000 | 06020601412 |
| 三臂聚乙二醇异氰酸酯 3-arm Poly(ethylene glycol) isocyanate | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\text{-NH}\left(\text{CH}_2\right)_6\text{NCO}\right\}_3$ | 3-arm PEG-NCO | | 2,000 | 06020603502 |
| | | | | 5,000 | 06020603506 |
| | | | | 10,000 | 06020603509 |
| | | | | 20,000 | 06020603512 |
| 三臂聚乙二醇叠氮化物 3-arm Poly(ethylene glycol) azide | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\text{-CH}_2\text{CH}_2\text{-N}_3\right\}_3$ | 3-arm PEG-N ₃ | | 2,000 | 06020603202 |
| | | | | 5,000 | 06020603206 |
| | | | | 10,000 | 06020603209 |
| | | | | 20,000 | 06020603212 |
| 三臂聚乙二醇炔 3-arm Poly(ethylene glycol) alkyne | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\text{-CH}_2\text{-C}\equiv\text{CH}\right\}_3$ | 3-arm PEG-Alkyne | | 2,000 | 06020603102 |
| | | | | 5,000 | 06020603106 |
| | | | | 10,000 | 06020603109 |
| | | | | 20,000 | 06020603112 |
| 三臂聚乙二醇丙烯酸酯 3-arm Poly(ethylene glycol) acrylate | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\text{-C}\left(\text{O}\right)\text{-CH=CH}_2\right\}_3$ | 3-arm PEG-AA | | 2,000 | 06020603302 |
| | | | | 5,000 | 06020603306 |
| | | | | 10,000 | 06020603309 |
| | | | | 20,000 | 06020603312 |
| 三臂聚乙二醇甲基丙烯酸酯 3-arm Poly(ethylene glycol) methacrylate | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\text{-C}\left(\text{O}\right)\text{-C}\left(\text{CH}_3\right)=\text{CH}_2\right\}_3$ | 3-arm PEG-MA | | 2,000 | 06020603402 |
| | | | | 5,000 | 06020603406 |
| | | | | 10,000 | 06020603409 |
| | | | | 20,000 | 06020603412 |
| 三臂聚乙二醇马来酰亚胺 (醚键) 3-arm Poly(ethylene glycol) maleimide(ether) | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\text{-CH}_2\text{CH}_2\text{-N}\left(\text{C}\left(\text{O}\right)\text{C}\left(\text{O}\right)\right)\right\}_3$ | 3-arm PEG-MAL | | 2,000 | 06020601702 |
| | | | | 5,000 | 06020601706 |
| | | | | 10,000 | 06020601709 |
| | | | | 20,000 | 06020601712 |
| | | | | 40,000 | 06020601715 |
| | | | | 2,000 | 06020601802 |

| | | | | |
|--------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|--------|-------------|
| 三臂聚乙二醇马来酰亚胺 (酯键) 3-arm Poly(ethylene glycol) maleimide(ester) | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\right\}_3\text{-CH}_2\text{CH}_2\text{-N}\left\{\begin{array}{c} \text{O} \\ \diagup \quad \diagdown \\ \text{C} \\ \diagdown \quad \diagup \\ \text{O} \end{array}\right\}_3$ | 3-arm PEG-MAL | 5,000 | 06020601806 |
| | | | 10,000 | 06020601809 |
| | | | 20,000 | 06020601812 |
| | | | 40,000 | 06020601815 |
| 三臂聚乙二醇马来酰亚胺 3-arm Poly(ethylene glycol) maleimide | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\right\}_3\text{-CH}_2\text{CH}_2\text{NH-C}\left(\text{O}\right)\text{-CH}_2\text{CH}_2\text{-N}\left\{\begin{array}{c} \text{O} \\ \diagup \quad \diagdown \\ \text{C} \\ \diagdown \quad \diagup \\ \text{O} \end{array}\right\}_3$ | 3-arm PEG-MAL | 2,000 | 06020601902 |
| | | | 5,000 | 06020601906 |
| | | | 10,000 | 06020601909 |
| | | | 20,000 | 06020601912 |
| | | | 40,000 | 06020601915 |
| 三臂聚乙二醇琥珀酰亚胺碳酸酯 3-arm Poly(ethylene glycol) succinimidyl ester | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\right\}_3\text{-C}\left(\text{O}\right)\text{-O-N}\left\{\begin{array}{c} \text{O} \\ \diagup \quad \diagdown \\ \text{C} \\ \diagdown \quad \diagup \\ \text{O} \end{array}\right\}_3$ | 3-arm PEG-SC | 2,000 | 06020602002 |
| | | | 5,000 | 06020602006 |
| | | | 10,000 | 06020602009 |
| | | | 20,000 | 06020602012 |
| | | | 40,000 | 06020602015 |
| 三臂聚乙二醇琥珀酰亚胺乙酸酯 3-arm Poly(ethylene glycol) succinimidyl carboxymethyl ester | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\right\}_3\text{-CH}_2\text{-C}\left(\text{O}\right)\text{-O-N}\left\{\begin{array}{c} \text{O} \\ \diagup \quad \diagdown \\ \text{C} \\ \diagdown \quad \diagup \\ \text{O} \end{array}\right\}_3$ | 3-arm PEG-SCM | 2,000 | 06020602202 |
| | | | 5,000 | 06020602206 |
| | | | 10,000 | 06020602209 |
| | | | 20,000 | 06020602212 |
| | | | 40,000 | 06020602215 |
| 三臂聚乙二醇琥珀酰亚胺琥珀酸酯 (酯键) 3-arm Poly(ethylene glycol) succinimidyl succinate | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\right\}_3\text{-CH}_2\text{CH}_2\text{-C}\left(\text{O}\right)\text{-O-N}\left\{\begin{array}{c} \text{O} \\ \diagup \quad \diagdown \\ \text{C} \\ \diagdown \quad \diagup \\ \text{O} \end{array}\right\}_3$ | 3-arm PEG-SS | 2,000 | 06020602502 |
| | | | 5,000 | 06020602506 |
| | | | 10,000 | 06020602509 |
| | | | 20,000 | 06020602512 |
| | | | 40,000 | 06020602515 |
| 三臂聚乙二醇琥珀酰亚胺琥珀酰胺酯 (酰胺键) 3-arm Poly(ethylene glycol) succinimidyl succinamide | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\right\}_3\text{-CH}_2\text{CH}_2\text{NH-C}\left(\text{O}\right)\text{-CH}_2\text{CH}_2\text{-C}\left(\text{O}\right)\text{-O-N}\left\{\begin{array}{c} \text{O} \\ \diagup \quad \diagdown \\ \text{C} \\ \diagdown \quad \diagup \\ \text{O} \end{array}\right\}_3$ | 3-arm PEG-SSA | 2,000 | 06020602602 |
| | | | 5,000 | 06020602606 |
| | | | 10,000 | 06020602609 |
| | | | 20,000 | 06020602612 |
| | | | 40,000 | 06020602615 |
| 三臂聚乙二醇琥珀酰亚胺戊二酸酯 (酯键) 3-arm Poly(ethylene glycol) succinimidyl glutarate | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\right\}_3\text{-C}\left(\text{O}\right)\text{-CH}_2\text{CH}_2\text{CH}_2\text{-C}\left(\text{O}\right)\text{-O-N}\left\{\begin{array}{c} \text{O} \\ \diagup \quad \diagdown \\ \text{C} \\ \diagdown \quad \diagup \\ \text{O} \end{array}\right\}_3$ | 3-arm PEG-SG | 2,000 | 06020602902 |
| | | | 5,000 | 06020602906 |
| | | | 10,000 | 06020602909 |
| | | | 20,000 | 06020602912 |
| | | | 40,000 | 06020602915 |
| 三臂聚乙二醇戊酰胺酯 (酰胺键) 3-arm Poly(ethylene glycol) succinimidyl glutaramide | $\text{CH}_3\text{-CH}_2\text{-C}\left\{\text{CH}_2\text{-O}\left(\text{CH}_2\text{CH}_2\text{O}\right)_n\right\}_3\text{-CH}_2\text{CH}_2\text{NH-C}\left(\text{O}\right)\text{-CH}_2\text{CH}_2\text{CH}_2\text{-C}\left(\text{O}\right)\text{-O-N}\left\{\begin{array}{c} \text{O} \\ \diagup \quad \diagdown \\ \text{C} \\ \diagdown \quad \diagup \\ \text{O} \end{array}\right\}_3$ | 3-arm PEG-SGA | 2,000 | 06020602802 |
| | | | 5,000 | 06020602806 |
| | | | 10,000 | 06020602809 |
| | | | 20,000 | 06020602812 |
| | | | 40,000 | 06020602815 |